

# Drying cabinet DC6-14 with heat pump

Drying Cabinets have no mechanical action and are used to efficiently dry bulky items such as workwear/overalls/gloves and boots or delicate items such as silk and linen



#### Priority on people

Ergonomic design, with user friendly positioning of door handle, control panel and suitable for disabled users

- $\cdot$  Easy operation with 2 automatic drying programs, which will stop once the load is dry
- · Braille script
- · Large doors and opening angles for easy access
- · One extensible hanger for easy loading/unloading
- · Hanging ability in the short end for smaller garments
- · Flexible installation with adjustable feet



# Long-term savings

By using a Drying Cabinet with a Heat Pump, not only can you avoid exhaust connection you can reach energy saving of 70% compared with an electric vented version. There are two options of heat pump version, one with water tank and one without



## Outstanding productivity

Time saving when used instead of flat or hang drying. The door can be opened a short moment without stopping the drying process  $\frac{1}{2} \int_{-\infty}^{\infty} \frac{1}{2} \int_{-\infty}^{$ 

### Safety

Option to activate child safety start lock



Images shown are a representation of the product only and variations may occur.

Main specifications <sup>1</sup>		DC6-14
Rated capacity	kg	10
Evaporation	g/min	80
Drying time	min	69
Rated input	kW	2.6
Energy/load of linen	kWh/kg	0.22
Energy/water evaporated	kWh/I	0.40


Electrical connections							
Heating alternative	Main voltage	Hz	Heating power kW	Total power kW	Recommen- ded fuse A		
Machines with heat pump	400V 3N~	50	1	3.2	10A slow- blow 10A automatic fuse		

<sup>1.</sup> Total power and recommended fuse does not depend on the heating power in those cases.

Sound levels		DC6-14	
Sound power/pressure level at drying <sup>1</sup>	dB(A)	<70	
Heat emission			
Average heat emission per drying cycle used to assess ventilation need <sup>2</sup>	kW	1.2	
Weight <sup>3</sup>			
	net, kg	250	
Operating panel Electrical connection	3. Drain for condense w	n for condense water ø 32 mm	

Colour of front and side panels is silver grey and handle is dark blue.







Sound power levels measured according to ISO 60704.
For assistance with dimensioning necessary ventilation needs, contact authorized ventilation technician. For sufficient ventilation all sources introducing heat need to be taken into account plus all other parameters effecting the ventilation need. Climate zone, building parameters, room size, etc.
Applies to assembled drying cabinets.