

# Washer extractor

H7-1100

## Features and benefits

- Flexibile Control programmable microprocessor with 9 fixed and up to 192 programs to allow free programming
- · High extraction for efficient dewatering
- · Frequency-controlled motor for optimal washing
- · Supplied with 8 + 5 signals for liquid detergents
- · Eight connections for liquid detergents
- · Large door opening for easy loading and unloading
- All critical parts made from stainless steel to provide a high level of corrosion resistance
- · Powder painted galvanised steel side panels
- Bearing seals lubricated with oil to ensure a long service life. Empty container alarm
- · Direct steam heating
- · Designed for easy servicing and maintenance

# Main options

- Forward or forward/backward tilting with full reversing function
- Five-compartment detergent box for powder detergent (located at the front or on the right hand side of the machine)
- · Third water valve
- · Large water valves
- · IS Integrated Saving
- · Connection to CMIS



Images shown are a representation of the product only and variations may occur.

Main specifications			H7-1100
Max. capacity		kg/lb	120/265
Drum, volume		litre	1100
diameter		ø mm	1220
Extraction		rpm	663
G-factor			300
Heating alternatives	steam		X
	non-heated		X
	electricity	kW	_
Consumption data "Norm	nal 60°C" *		
Total time (cold+hot/cold)		min	40/45
Water consumption (cold/hot)		litre	533/153
Energy consumption (motor/heating)		kWh	2.4/-
Steam consumption (cold/hot)		kg	12
Steam consumption (cold)		kg	23
* With filling factor 1:10. Water temperature 15°C cold water and 65°C hot water.		ter.	

Produced according to ISO 9001 and ISO 14001.



Electrical connections					
Heating alternative	Main voltage	Hz	Heating power kW	Total power kW	Recommended fuse A
Steam or Non heated	220-240V 3 ~ 380-480V 3 ~	50/60 50/60	-	6.3 6.3	25 16

Water, steam and air connections	H7-1100		
Water valves Rec. Water pressure Function limits for water valve Capacity at 300 kPa Drain valve Draining capacity Steam valve Rec. Steam pressure Function limits for steam valve Compressed air Air pressure Air consumption Five-compartment detergent injector	DN kPa kPa I/min ø mm I/min DN kPa DN kPa I/h	32 200-600 50-1000 150 110 400 32 300-600 50-800 6 500-700 20 20	
Floor requirements			
Frequency of the dynamic force Floor load at max extraction	Hz kN	11.1 27.9 ± 2.0	
Sound levels			
Sound pressure level* With insulation	dB(A) dB(A)	73 < 70	
Heat emission			
% of installed power, max 90°		6.8	
Shipping data**			
Shipping volume	net, kg m³	2300 8.4	


 $<sup>^{\</sup>ast}$   $\,\,$  A-weighted emmission sound pressure level at working stations.

<sup>\*\*</sup> Average data. Crated weight/shipping volume depends on configuration. Please contact logistics for exact measures.




Dimensions in mm	H7-1100		
A Width B Depth C Height std/tilt+IWS D std/tilt+IWS Ea	1640 1850 2190/2230 955/995 300		
F std/tilt+IWS G	380 2095/2135 1070 830		
	635 445 1140		
M std/tilt+IWS N std/tilt+IWS O P	1660/1660 395/435 820 2400		
R S T U	1160 2480 955 240 335		


- 1 Control panel
- 2 Door opening ø 700 mm
- **3a**Five-compartment detergent box, front (optional)
- **3b**Five-compartment detergent box, right hand side (optional)
- 4 Cold water connection
- **5** Hot water connection
- **6** Third water connection (optional)
- 7 Steam connection
- 8 Drain
- 9 Electrical connection
- 10 Compressed air connection
- 11 External liquid detergent injector, 6 pcs ø 10, 1 pc ø 16 and 1 pc ø 20
- **12** Water connection, detergent injector (optional)



Front



Right side



S T R

The movement when tilting



## **Options**

- · Forward or forward/backward tilting with drum reversal makes unloading into a trolley easy.
- Five-compartment detergent box.
   Option 1, (5x1 litre), located on front of the machine.
   Option 2, (5x2 litres), located on right hand side of the machine.
- Third water valve electrically-controlled water valve for hard water.
- · Steam connection components.
- · Connection components for 2 water connections.
- · Connection components for 3 water connections.
- · IS Integrated Saving
- · Large water valves (DN 50 / 2" BSP) (DN 40 / 11/2" BSP).
- · Kit for connection to CMIS (Certus Management Information Systems) network.

#### Accessory

• PC program. Allows the creation of wash programs on a PC and their transference to the machine via a memory card.



CMIS can be fitted to washer extractors with Clarus Control, tumble dryers with Selecta Control and ironers with electronic control system. All you need to access and view the statistical feedback is a normal PC.